


TECHSPEC® 19.1 x 12.7mm 266nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#39-590** ☒ In Stock



1



€156,00

ADD TO CART

Qty 1-5

€156,00

Qty 6+

€137,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%) 85
Back Surface: Commercial Polish
Reflection at DWL (%) 99.8
Coating Specification: R_{abs} >99.8% @ 266nm
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (266nm)
Design Wavelength DWL (nm): 266
Dimensions (mm): 19.1 x 12.7 +0.00/-0.10
Thickness (mm): 6.35 ±0.20
Angle of Incidence (°): 0-45
Substrate: Fused Silica (Corning 7980)
Damage Threshold, Reference: 2 J/cm² @ 266nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View