

TECHSPEC® 16mm, f/2.8 Ci Series Fixed Focal Length Lens



16mm Focal Length

Stock **#85-350** 3-4 DAYS



1



€215,00

ADD TO CART

Qty 1+

€215,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Iris Option:
Fixed

Length (mm):
40.80

Horizontal Field of View, 1/2" Sensor:
44.5mm - 22.7°

Horizontal Field of View, 2/3" Sensor:
61.4mm - 30.9°

Filter Thread:

M25.5 x0.50 with required adapter #89-941
Maximum Diameter (mm): 26.5
Weight (g): 37
Horizontal Field of View, 1/3" Sensor: 33.3mm - 17.1°
Maximum Rear Protrusion (mm): 1.09
Maximum Image Circle (mm): 11.00
Numerical Aperture NA, Object Side: 0.0235
Horizontal Field of View @ Max Sensor Format: 61.4mm - 30.9°
Number of Elements (Groups): 7 (6)
Horizontal Field of View, 1/1.8" Sensor: 50.1mm - 25.2°
Front Thread: M22.0 x0.75 (Male)
Horizontal Field of View, 1/2.5" Sensor: 39.6mm - 20.2°
Type: Fixed Focal Length Lens
Diameter (mm): 26.50
Focal Length FL (mm): 16.00
Primary Magnification PMAG: 0.149
Maximum Sensor Format: 2/3"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/2.8
Coating: 425 - 675nm BBAR
Coating Specification: 425 - 675nm BBAR
Entrance Pupil Position (mm): 19.19
Horizontal Field of View, 1/4" Sensor: 25mm - 12.8°
Object Space Principal Plane (mm): 21.30
Image Space Principal Plane (mm): -3.00
Field of View at Max Sensor Format: Horizontal: 59.7mm - 30.9° Vertical: 44.6mm - 23.4° Diagonal: 75mm - 38.2°
Maximum Distortion (%): -0.77
Exit Pupil Position (mm): -5.43
Lens Wavelength Range: VIS
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

