

TECHSPEC® 19.1mm Dia., 6.35mm Thick, N-BK7 Uncoated Laser Window Substrate



TECHSPEC® Uncoated Laser Window Substrates

Stock #38-056 In Stock

⊖ 1 ⊕ **€120,00**

ADD TO CART

Qty 1-5

€120,00

Qty 6+

€108,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
17.19

Coating:
Uncoated

Diameter (mm):

19.10 +0.00/-0.10

Substrate:
[N-BK7](#)

Index of Refraction n_d :
1.516

Surface Quality:
10-5

Thickness (mm):
6.35 ±0.20

Type:
Laser Window Substrate

Parallelism (arcmin):
<3

Bevel:
Protective as needed

Clear Aperture (%):
90

Abbe Number (v_d):
64.17

Wavelength Range (nm):
350 - 2200

Surface Flatness (P-V):
λ/10

Edges:
Fine Ground

Type of Window:
Glass

Regulatory Compliance

RoHS 2015:
[Compliant](#)

REACH 201:
[Compliant](#)

Certificate of Conformance:
[View](#)