

TECHSPEC® 1X-8X Magnification, NIR I Coated, Adjustable Mounted Anamorphic Prism Pair



1X-8X Magnification, NIR I Coated, Adjustable Mounted Anamorphic Prism Pair

Stock **#34-553** 3-4 DAYS



1



€475,00

ADD TO CART

Qty 1-5

€475,00

Qty 6+

€380,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
NIR I (600-1050nm)

Angle Tolerance (arcmin):
3

Coating Specification:
R_{avg} ≤0.5% @ 600 - 1050nm

Dimensions (mm): 52 x 27.7 x 35.6
Magnification: 1X-8X (with 1mm Dia. Minor Axis Input Beam)
Mount: Mounted (Adjustable Magnification)
Substrate: ☐ N-SF11
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Type: Beam Shaping
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View