

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

Richardson Gratings™ 1800 Grooves, 30 X 30mm, 190-900nm, Plane Holographic Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Reflective Holographic Diffraction Gratings



Stock #15-750 3-4 DAYS



€175,00

ADD TO CART

Qty 1+

€175,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
1800

Wavelength Range (nm):

190 - 900
Blaze Wavelength (nm): 250
Dimensions (mm): 30.0 x 30.0 ±0.1
Clear Aperture (%): >90
Coating: Aluminium
Construction: Holographic Grating
Length (mm): 30.00
Substrate: ☐ Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 30.00
Reflected Wavefront, RMS: $\lambda/4$
Centering of Ruled Area on Substrate (mm): ±1
Alignment of Grooves to Edge (°): ±0.15
Groove Spacing Tolerance (%): <0.05
Polarization: S, P and Average
Master Reference: 300H
Spectral Order (m): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View