

TECHSPEC® 20.0mm Dia. x 150.0mm FL, MgF₂ Coated, Plano-Convex Lens



Stock #45-277 In Stock

[Other Coating Options](#)

1 **€35,00**

ADD TO CART

Qty 1-9

€35,00

Qty 10+

€31,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm):
150.00 @ 587.6nm

Back Focal Length BFL (mm):
148.02

Coating:
MgF₂ (400-700nm)

Coating Specification:
R_{avg} ≤ 1.75% @ 400 - 700nm

Substrate:
[N-BK7](#)

Surface Quality:
40-20

Power (P-V) @ 632.8nm:
1.5λ

Irregularity (P-V) @ 632.8nm:
λ/4

Focal Length Tolerance (%):
±1

Centering (arcmin):
<1

Center Thickness CT (mm):
3.00 ± 0.10

Edge Thickness ET (mm):
2.35

Radius R₁ (mm):
77.52

Clear Aperture CA (mm):
19

f#:
7.5

Numerical Aperture NA:
0.07

Type:
Plano-Convex Lens

Bevel:
Protective bevel as needed

Wavelength Range (nm):
400 - 700

Damage Threshold, By Design:
10 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 219:
[Compliant](#)

Certificate of Conformance:
[View](#)