

TECHSPEC® 18mm Dia. x 60mm FL, VIS 0° Coated, Achromatic Lens



Stock **#47-709** ☐ In Stock
[Other Coating Options](#)

1 **€98,00**

ADD TO CART

Qty 1-5
€98,00
Qty 6+
€78,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
18.00 +0.0/-0.025

Effective Focal Length EFL (mm):

60.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 56.79
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 17.00
Centering (arcmin): <1
Center Thickness CT (mm): 5.85 ±0.20
Center Thickness CT 1 (mm): 3.85 ±0.10
Center Thickness CT 2 (mm): 2.00 ±0.10
Radius R ₁ (mm): 42.51
Radius R ₂ (mm): -26.24
Radius R ₃ (mm): -226.77
Edge Thickness ET (mm): 4.71
Substrate:  N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 3.33
Numerical Aperture NA: 0.15
Coating: VIS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View