

203.2mm Clear Aperture 50R/50T, Pellicle Beamsplitter



Pellicle Beamsplitters

Stock #19-311 3-4 DAYS

- 1 + **€1.982,00**

ADD TO CART

Qty 1+

€1.982,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
203.2

Coating:
Dielectric

Coating Specification:
50/50 @ 632.8nm

Construction:
Pellicle

Design Wavelength DWL (nm): 632.8
Diameter (mm): 222.25
Housing: Black Anodized Aluminum
Index of Refraction n_d: 1.5
Mount Thickness (mm): 9.53
Reflection/Transmission Ratio (R/T): 50/50 ±5%
Substrate: Nitrocellulose
Surface Quality: 40-20
Type: Pellicle Beamsplitter
Mounting Threads: 6-32
Thickness (μm): 2 +0.3/-0.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View