

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 19.1mm Dia., 6.35mm Thick, 532nm, N/10 Fused Silica Window



TECHSPEC N/10 Laser Line Coated Windows

Stock **#38-968** 3-4 DAYS



1



€142,50

ADD TO CART

Qty 1-5

€142,50

Qty 6+

€114,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):

0

Clear Aperture CA (mm):

17.19

Coating:

Laser V-Coat (532nm)

Design Wavelength DWL (nm): 532
Diameter (mm): 19.10 +0.00/-0.10
Substrate: ☐ Fused Silica (Corning 7980)
Index of Refraction n_d: 1.458
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Laser Line Window
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%): 90
Abbe Number (v_d): 67.8
Coating Specification: R _{abs} <0.25% @ 532nm
Surface Flatness (P-V): λ/10
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 20ns, 20Hz
Fused Silica Grade: 7980 0F
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View