


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Roll of Spectral Black/Metal Velvet



Stock #17-445 3-4 DAYS



1



€3.565,00

ADD TO CART

Qty 1+

€3.565,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:
Metal Velvet™

Model Number:
MRR-20x2500-3

Operating Temperature (°C):

-40 to +150
Type: Low Outgassing Adhesive
Coating Thickness (µm): 5 - 8
Foil Thickness (µm): 115
Abrasion Resistance: Light, do not touch
Adhesive Thickness (µm): 60
Humidity Resistance: ML-C-48497A
Wavelength Range (µm): 0.3 - 14
Dimensions (cm): 20 x 2500
Note: Typical Adhesive Outgassing Performance: 0.85% TML, 0% VCM per ASTM E595-77/84/90

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant