

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 20mm Dia X 16mm FL, NIR I Coated, Molded Aspheric Condenser Lens



TECHSPEC Molded Aspheric Condenser Lenses

Stock #15-731 3-4 DAYS

[Other Coating Options](#)

- 1 +

€58,00

ADD TO CART

Qty 1-10

€58,00

Qty 11+

€51,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.2

Effective Focal Length EFL (mm):
16.00 @ 587.6nm

Numerical Aperture NA:

0.625
Back Focal Length BFL (mm): 9.13
Substrate: ☐ Liba2000+
Focal Length Tolerance (%): ±5
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Centering (arcmin): ≤25
Surface Quality: Molded Side: 5/3 x 0.4; E 0.2 Polished Side: 5/3 x 0.25; E 0.2
Clear Aperture CA (mm): 17.77
Edge Thickness ET (mm): 3.21
Center Thickness CT (mm): 10.45 ±0.30
f/#: 0.8
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 20.00
Radius R₂ (mm): ∞
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant