

20mm Dia. x 17.5mm FL, NIR I Coated, Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock **#15-891** 3-4 DAYS

[Other Coating Options](#)

-

1

+

€64,00

ADD TO CART

Qty 1-10
€64,00

Qty 11+
€56,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
20.00 +/-0.3

Effective Focal Length EFL (mm):
17.50 @ 587.6nm

Numerical Aperture NA:
0.57

Back Focal Length BFL (mm): 12.40
Substrate:  Liba2000+
Focal Length Tolerance (%): ±7
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Centering (arcmin): ≤30
Surface Quality: 5/3 x0.4; E 0.2
Clear Aperture CA (mm): 16.00
Edge Thickness ET (mm): 2.3
Center Thickness CT (mm): 8.30 +/-0.20
f/#: 0.88
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 20.0
Radius R₂ (mm): 117.5
Shape of Back Surface: Convex
Type: Condenser Lens
Wavelength Range (nm): 600 - 1050
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant