

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

2050nm Flat Top Beam Shaper | πSnaper 6_6_2.05

See More by [AdiOptica](#)



Flat Top Beam Shaper

Stock #12-242 3-4 DAYS



1



€6.268,00

ADD TO CART

Qty 1-4

€6.268,00

Qty 5+

€5.639,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
2050

Diameter (mm):
39.00

Entrance Beam Diameter, 1/e² (mm):
6.4 - 6.5

Model Number: πShaper 6_6_2.05
Length (mm): 143.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <270
Wavelength Range (nm): 1900 - 2160
Style: Flat Top
Damage Threshold, By Design: ☐ 50 mJ/cm ² @ 5ns (typical)
Output Diameter, FWHM (mm): 6.4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant