

TECHSPEC® 20mm, 1064nm V-Coat, Fused Silica High Power Laser Line RA Prism



Stock **#83-333** 3-4 DAYS

- 1 + **€162,00**

ADD TO CART

Qty 1-5
€162,00

Qty 6+
€129,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle Tolerance (arcsec):
±40

Coating:
Laser V-Coat (1064nm)

Design Wavelength DWL (nm):
1064

Substrate: ☐ Fused Silica (Coming 7980)
Surface Quality: 20-10
Type: Right Angle Prism
Dimensional Tolerance (mm): +0.00/-0.10
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 28.30
Length of Legs (mm): 20.00
Pyramid Tolerance (arcmin): ±1
Image Orientation: Left-Handed
Coating Specification: R_{abs} <0.25% @ 1064nm
Ray Deviation (°): 90
Surface Flatness (P-V): λ/10
Damage Threshold, By Design: ☐ 15 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View