

TECHSPEC® 20mm Dia., 2mm Thick, NIR I AR Coated Sapphire Window



Stock **#36-498** 3-4 DAYS

⊖ 1 ⊕ **€97,50**

ADD TO CART

Qty 1-24
€97,50
Qty 25+
€78,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
72.24

Axis Orientation:
Random

Bevel:
Protective as needed

Birefringence (n_o-n_e): 0.008 for Visible Light Orthogonal to Optical Axis
Clear Aperture (%): ≥90
Clear Aperture CA (mm): 18.00
Diameter (mm): 20.00 ±0.10
Thickness (mm): 2.00 ±0.10
Coating: NIR I (600-1050nm)
Coating Specification: R_{avg} ≤0.5% @ 600 - 1050nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 8.8
Density (g/cm³): 3.97
Edges: Fine Ground
Index of Refraction n_d: 1.77
Knoop Hardness (kg/mm²): 1900
Parallelism (arcmin): ≤3.5
Poisson's Ratio: 0.27
Substrate: Sapphire (Al₂O₃)
Surface Flatness (P-V): 2λ (typical)
Surface Quality: 80-50
Type: Protective Window
Wavelength Range (nm): 600 - 1050
Young's Modulus (GPa): 435

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant