

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #18-301 3-4 DAYS



1



€25,00

ADD TO CART

Qty 1-5

€25,00

Qty 6+

€20,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):
22.50 x 22.50

Dimensions (mm): 25.00 x25.00 ±0.25
Thickness (mm): 0.40 ±0.05
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 7.2 (+20 to +300°C)
Density (g/cm³): 2.51
Edges: Cut and Seamed
Index of Refraction n_d: 1.523
Poisson's Ratio: 0.21
Substrate: D263@Teco
Surface Quality: 80-50
Transformation Temperature (°C): 557
Type: Protective Window
Wavelength Range (nm): 350 - 2000
Young's Modulus (GPa): 72.9
Length (mm): 25.00
Width (mm): 25.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant