

TECHSPEC® 20mm Dia. x 30mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock **#45-175** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€95,00**

ADD TO CART

Qty 1-5
€95,00

Qty 6+
€76,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm): 30.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 24.70
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 19.00
Centering (arcmin): <1
Center Thickness CT (mm): 10.16 ±0.20
Center Thickness CT 1 (mm): 8.40 ±0.10
Center Thickness CT 2 (mm): 1.76 ±0.10
Radius R₁ (mm): 21.41
Radius R₂ (mm): -13.75
Radius R₃ (mm): -105.58
Edge Thickness ET (mm): 7.21
Substrate: S-BAH11 / N-SF10
Surface Quality: 40-20
f/#: 1.5
Numerical Aperture NA: 0.33
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View