

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC X10 Laser Line Coated Windows

Stock #48-211 □ In Stock



1



€155,00

ADD TO CART

Qty 1-5

€155,00

Qty 6+

€124,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):

0

Clear Aperture CA (mm):

22.50

Coating:

Laser V-Coat (1064nm)

Design Wavelength DWL (nm): 1064
Diameter (mm): 25.00 +0.00/-0.10
Substrate: Fused Silica Excimer Grade (Coming 7980 KrF)
Index of Refraction n_d: 1.458
Surface Quality: 10-5
Thickness (mm): 3.00 ±0.10
Type: Laser Line Window
Bevel: Protective as needed
Clear Aperture (%): 90
Transmitted Wavefront, P-V: λ/10
Abbe Number (v_d): 67.8
Parallelism (arcsec): ≤5
Coating Specification: R_{abs} <0.25% @ 1064nm
Damage Threshold, By Design: 15 J/cm² @ 1064nm, 20ns, 20Hz
Fused Silica Grade: 7980 KrF 0A
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View