

20X DIN Achromatic Finite Intl Standard Objective



Stock #33-438 3-4 DAYS

⊖ 1 ⊕ **€147,00**

ADD TO CART

Qty 1+
€147,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm): 546
Field of View (mm): 1
Focal Length FL (mm): 8.00
Length excluding Threads (mm): 41.70
Magnification: 20X

Maximum Diameter (mm): 25
Numerical Aperture NA: 0.40
Mounting Threads: RMS / 20.32mm x36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 160mm
Type: Achromatic
Depth of Field (µm): 4.98
Field of View, 18 Diameter Field Eyepiece (mm): 0.90
Operating Temperature (°C): +10 to +40
Operating Humidity: Max 85% at 35°C with no condensation
Working Distance (mm): 0.8
Weight (g): 63.8
Wavelength Range (nm): 400 - 700
Style: Finite Conjugate
Field Number (mm): 20
Parfocal Length (mm): 42.5
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View