


TECHSPEC® 25.4 x 25.4mm Protected Silver, 4-6λ Mirror



Stock **#36-044** ☐ In Stock

-

1

+

€31,50

ADD TO CART

Qty 1-5
€31,50
Qty 6+
€23,50
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensions (mm):

25.4 x 25.4
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 24.13 x 24.13
Edges: Seamed, 0.5mm Maximum Edge Chip
Thickness (mm): 3.00
Type: Flat Mirror
Wavelength Range (nm): 450 - 10000
Length (mm): 25.40
Width (mm): 25.40
Damage Threshold, By Design: ☐ 0.5 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
