

TECHSPEC® 25.0mm Diameter x 40.0mm FL, 405nm V-Coat, PCX Lens



633nm Laser Line Coated Plano-Convex (PCX) Lenses



Stock #69-347 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€55,00**

ADD TO CART

Qty 1-9

€55,00

Qty 10+

€49,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):
40.00 @ 587.6nm

Back Focal Length BFL (mm):
36.31

Coating:
Laser V-Coat (405nm)

Coating Specification:
 $R_{\text{abs}} < 0.25\%$ @ 405nm

Substrate:
[N-BK7](#)

Surface Quality:
40-20

Power (P-V) @ 632.8nm:
 1.5λ

Irregularity (P-V) @ 632.8nm:
 $\lambda/4$

Focal Length Tolerance (%):
 ± 1

Centering (arcmin):
<1

Center Thickness CT (mm):
 5.60 ± 0.10

Edge Thickness ET (mm):
1.39

Radius R_1 (mm):
20.67

Clear Aperture CA (mm):
24

f#:
1.6

Numerical Aperture NA:
0.31

Design Wavelength DWL (nm):
405

Type:
Plano-Convex Lens

Bevel:
Protective bevel as needed

Damage Threshold, By Design:
 3 J/cm^2 @ 405nm, 10ns

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)