


TECHSPEC® 25.4 x 25.4mm 1064nm 45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#39-655** 3-4 DAYS



1



€161,00

ADD TO CART

Qty 1-5

€161,00

Qty 6+

€141,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%) 85
Back Surface: Commercial Polish
Reflection at DWL (%) 99.8
Coating Specification: R_{abs} >99.8% @ 1064nm R_{avg} >99.5% @ 1046 - 1074nm
Wavelength Range (nm) 1046 - 1074
Surface Flatness (P-V) λ/10
Coating Type: Dielectric
Coating: Laser Mirror (1046-1074nm)
Design Wavelength DWL (nm) 1064
Dimensions (mm) 25.4 x 25.4 +0.00/-0.10
Thickness (mm) 6.35 ±0.20
Angle of Incidence (°) 45
Substrate: Fused Silica (Corning 7980)
Damage Threshold, Reference: 20 J/cm² @ 1064nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View