


TECHSPEC® 25.4 x 25.4mm 355nm 0-45°, Nd:YAG Laser Line Mirror



TECHSPEC® Nd:YAG Laser Line Mirrors

Stock **#39-624** 3-4 DAYS



1



€172,00

ADD TO CART

Qty 1-5

€172,00

Qty 6+

€152,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
10-5

Type:
Laser Mirror

Parallelism (arcmin):
<3

Clear Aperture (%) 85
Back Surface: Commercial Polish
Reflection at DWL (%) 99.8
Coating Specification: R_{abs} >99.8% @ 355nm
Surface Flatness (P-V): λ/10
Coating Type: Dielectric
Coating: Laser Mirror (355nm)
Design Wavelength DWL (nm): 355
Dimensions (mm): 25.4 x 25.4 +0.00/-0.10
Thickness (mm): 6.35 ±0.20
Angle of Incidence (°): 0-45
Substrate: Fused Silica (Coming 7980)
Damage Threshold, Reference: 5 J/cm² @ 355nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View