

In order to provide more accurate inventory information, please select your shipping country:


Select Your Country/Region: European Union



SUBMIT

SCHOTT AS87 ECO, 25.4 X 76.2mm, 0.1mm Thick, Ultra-Thin window

See More by [SCHOTT Optical Components](#)



Stock #12-315 3-4 DAYS



1



€36,00

ADD TO CART

Qty 1-10

€36,00

Qty 11+

€28,75

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Abbe Number (v_d):

59.5

Bevel:

Protective as needed

Clear Aperture (%):

90

Clear Aperture CA (mm): 22.86 x 68.58
Dimensions (mm): 25.40 x 76.20
Thickness (mm): 0.10 ±0.01
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 8.7
Density (g/cm³): 2.46
Index of Refraction n_d: 1.504
Knoop Hardness (kg/mm²): 500
Poisson's Ratio: 0.216
Substrate: AS 87 ECO
Surface Quality: 80-50
Type: Protective Window
Wavelength Range (nm): 200 - 3200
Young's Modulus (GPa): 73.3
Length (mm): 76.20
Width (mm): 25.40

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant