


254 x 304.8 x 1mm High Efficiency Window



Stock #63-221 ☐ In Stock

-

1

+

€87,50

ADD TO CART

Qty 1-5
€87,50
Qty 6+
€70,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0

Bevel:
Protective as needed

Clear Aperture (%):
≥90

Clear Aperture CA (mm): 228.6 x 274.32
Dimensions (mm): 254.00 x 304.80
Thickness (mm): 1.00 ±0.25
Coating: BBAR (425-700nm)
Coating Specification: R _{avg} ≤0.5% @ 425 - 700nm
Edges: Seamed
Substrate: Float Glass
Surface Quality: 80-50
Transmission (%): 96.9 Average (typical)
Type: Protective Window
Wavelength Range (nm): 425 - 700
Length (mm): 304.80
Width (mm): 254.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant