

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25.4mm Dia., 532nm T, 355nm R 45° Harmonic Separator



TECHSPEC Nd:YAG Harmonic Separators

Stock #37-719 3-4 DAYS



1



€268,00

ADD TO CART

Qty 1-5

€268,00

Qty 6+

€241,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
45

Clear Aperture (%):
>85

Coating Specification:
Surface 1: R_{abs}: >99% @ 355nm, T_{abs}: >95% @ 532nm

Surface 2: R _{abs} : <0.5% @532nm
Construction: Dichroic
Diameter (mm): 25.40 +0.00/-0.10
Parallelism (arcmin): <3
Reflection Wavelength (nm): 355
Substrate: ☐ Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Transmission Wavelength (nm): 532
Type: Harmonic Beamsplitter
Damage Threshold, By Design: ☐ Surface 1: 2.5 J/cm ² @ 355nm, 20ns, 20Hz 5 J/cm ² @ 532nm, 20ns, 20Hz Surface 2: 10 J/cm ² @ 532nm, 20ns, 20Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View