

TECHSPEC® 25.4 x 76.2mm EFL 90° Protected Gold 100Å Off-Axis Parabolic Mirror



Stock **#35-529** 3-4 DAYS

[Other Coating Options](#)

- 1 + **€295,00**

ADD TO CART

Qty 1-5
€295,00

Qty 6+
€265,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
25.40 +0.00/-0.38

Effective Focal Length EFL (mm):

76.20
Focal Length Tolerance (%) : ±1
Radius of Curvature (mm) : 76.20
Coating : Protected Gold (700-10000nm)
Coating Type : Metal
Coating Specification : R _{avg} ≥94% @ 700 - 800nm R _{avg} ≥97% @ 800 - 2,000nm R _{avg} ≥98% @ 2,000 - 12,000nm
Off-Set Angle (°) : 90
Parent Focal Length PFL (mm) : 38.1
Surface Figure, RMS : λ/4
Surface Roughness (Angstroms) : <100 RMS
Wavelength Range (nm) : 700 - 10000
Clear Aperture (%) : 90
Surface Quality : 80-50
Compatible Mounting Plates : #47-111
Substrate : Aluminum 6061-T6
Y Offset (mm) : 76.2
Reflected Wavefront, RMS : λ/2

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant