

TECHSPEC® 25.4 x 646mm EFL 15° Protected Aluminum 100Å Off-Axis Parabolic Mirror



Stock **#35-540** [CONTACT US](#)

[Other Coating Options](#)

- 1 + **€245,00**

ADD TO CART

Qty 1-5
€245,00

Qty 6+
€220,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
25.40 +0.00/-0.38

Effective Focal Length EFL (mm):

646.00
Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 1,270.00
Coating: Protected Aluminum (400-2000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥85% @400 - 700nm R _{avg} ≥97% @2,000 - 12,000nm
Off-Set Angle (°): 15
Parent Focal Length PFL (mm): 635.00
Surface Figure, RMS: λ/4
Surface Roughness (Angstroms): <100 RMS
Wavelength Range (nm): 400 - 2000
Clear Aperture (%): 90
Surface Quality: 80-50
Compatible Mounting Plates: #47-111
Substrate: Aluminum 6061-T6
Y Offset (mm): 167.2
Reflected Wavefront, RMS: λ/2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant