

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

25.4mm $\varnothing$, 1030nm Highly-Dispersive Ultrarast Mirror

See More by [UltraFast Innovations \(UFI\)](#)



Stock #12-335 3-4 DAYS



1



€738,00

ADD TO CART

Qty 1-3

€738,00

Qty 4+

€650,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Design Wavelength DWL (nm):
1030

Wavelength Range (nm):
1010 - 1070

Diameter (mm):
25.40 +0.0/-0.1

Angle of Incidence (°): 7
Reflection at DWL (%): 99.9 (typical, s-polarization)
Thickness (mm): 6.35 ±0.2
Substrate: Fused Silica (Coming 7980)
Type: Laser Mirror
Coating Type: Dielectric
Coating Specification: R_{avg} >99.8%, GDD = -1000fs² @ 1010 - 1070nm (s-polarization) R_{abs} >99.9% @ 1030nm (typical, s-polarization)
GDD Specification: -1000fs² @ 1010 - 1070nm
Back Surface: Commercial Polish
Clear Aperture (%): 80
Coating: Ultrafast (1010-1070nm)
Typical Applications: Yb:doped 1st Harmonic
Irregularity (P-V) @ 632.8nm: λ/10
Wedge (arcmin): 10 ±5
Minimum Reflectivity : >99.8% @ 1010 - 1070nm (s-polarization)
Damage Threshold, By Design: 0.3 J/cm² @ 1030nm, 50fs, 1kHz, 100µm Beam Diameter

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant