

**TECHSPEC® 25.4mm Dia. 266nm, Nd:YAG Laser Line Beam Sampler**



TECHSPEC® Nd:YAG Laser Line Beam Samplers

Stock **#38-993** 3-4 DAYS



1



**€152,50**

ADD TO CART

Qty 1-5

€152,50

Qty 6+

€137,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Angle of Incidence (°):**  
0 ±5

**Clear Aperture (%):**  
90

**Coating:**  
Laser V-Coat (266nm)

|                                                                                                       |
|-------------------------------------------------------------------------------------------------------|
| <div>Coating Specification:</div> <div>R<sub>abs</sub> &lt;0.25% @ 266nm</div>                        |
| <div>Design Wavelength DWL (nm):</div> <div>266</div>                                                 |
| <div>Diameter (mm):</div> <div>25.40 +0.00/-0.10</div>                                                |
| <div>Index of Refraction n<sub>d</sub>:</div> <div>1.458</div>                                        |
| <div>Parallelism (arcmin):</div> <div>&lt;3</div>                                                     |
| <div>Substrate: <div></div></div> <div><a href="#">Fused Silica</a> (Corning 7980)</div>              |
| <div>Surface Flatness (P-V):</div> <div>λ/10</div>                                                    |
| <div>Surface Quality:</div> <div>10-5</div>                                                           |
| <div>Thickness (mm):</div> <div>6.35 ±0.20</div>                                                      |
| <div>Type:</div> <div>Beam Sampler</div>                                                              |
| <div>Damage Threshold, By Design: <div></div></div> <div>3 J/cm<sup>2</sup> @ 266nm, 20ns, 20Hz</div> |

## Regulatory Compliance

|                                                                        |
|------------------------------------------------------------------------|
| <div>RoHS 2015:</div> <div><a href="#">Compliant</a></div>             |
| <div>Reach 209:</div> <div><a href="#">Compliant</a></div>             |
| <div>Certificate of Conformance:</div> <div><a href="#">View</a></div> |