

TECHSPEC® 25.4mm Dia. x 25mm EFL, Uncoated, Concave Laser Mirror



TECHSPEC Uncoated Concave Mirrors

Stock **#39-973** 3-4 DAYS



1



€108,00

ADD TO CART

Qty 1-5

€108,00

Qty 6+

€96,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate: ☐ [Fused Silica](#) (Coming 7980)

Surface Quality:
20-10

Diameter (mm):
25.40 +0.00/-0.20

Effective Focal Length EFL (mm): 25.00
Radius of Curvature (mm): 50.00
Coating: Uncoated
Back Surface: Fine Grind
Center Thickness CT (mm): 4.71
Clear Aperture (%): 90
Edge Thickness ET (mm): 6.35 ±0.10
Radius R₁ (mm): 50.00
Type: Concave Mirror
Irregularity (P-V) @ 632.8nm: λ/10

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View