

25.4mm Dia 80R/20T, UV-NIR Polka-Dot Beamsplitter



Stock #18-716 3-4 DAYS

⊖ 1 ⊕

€188,00

ADD TO CART

Qty 1-10
€188,00

Qty 11+
€159,80

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0 - 45

Center to Center Spacing (mm):
0.15

Clear Aperture (%):
90

Coating: Square Aluminum (AlMgF ₂) Apertures
Construction: Polka-Dot
Diameter (mm): 25.40
Dimensional Tolerance (mm): +0.0/-0.5
Minimum Aperture (mm): 2.00
Operating Temperature (°C): 150 Maximum
Parallelism (arcmin): <3
Reflection/Transmission Ratio (R/T): 80/20
Reflection/Transmission Tolerance (%): ±5 @45°
Substrate: Fused Silica (Corning 7980)
Surface Quality: 80-50
Thickness (mm): 1.65 ±0.1
Type: Standard Beamsplitter
Wavelength Range (nm): 250 - 2000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View