

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25.4mm Dia. x 50mm EFL, 266nm U-45°, Concave Laser Line Mirror



Laser Line Concave Mirrors

Stock #39-948 ☒ In Stock



1



€160,00

ADD TO CART

Qty 1-5

€160,00

Qty 6+

€144,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Design Wavelength DWL (nm):

266

Substrate: ☐

[Fused Silica](#) (Corning 7980)

Surface Quality:

20-10

Diameter (mm): 25.40 +0.00/-0.20
Effective Focal Length EFL (mm): 50.00
Radius of Curvature (mm): 100.00
Coating: Laser Mirror (266nm)
Coating Specification: R_{abs} >99.80% @ 266nm (0-45° AOI)
Coating Type: Dielectric
Back Surface: Fine Grind
Center Thickness CT (mm): 5.54
Clear Aperture (%): 90
Edge Thickness ET (mm): 6.35 ±0.10
Radius R₁ (mm): 100.00
Type: Concave Mirror
Wavelength Range (nm): 263 - 268
Irregularity (P-V) @ 632.8nm: λ/10
Damage Threshold, Reference: 1 MW/cm² @ 266nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View