


TECHSPEC®

25.4mm Diameter x 1000mm FL, 1900-2200nm Coated, IR Ultrafast Thin PCX Lens



Stock #11-630 3-4 DAYS

[Other Coating Options](#)



1



€182,00

ADD TO CART

Qty 1-5

€182,00

Qty 6+

€159,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):
1,001.17 @587.6nm

Back Focal Length BFL (mm): 1000.07
Coating: BBAR (1900-2200nm)
Coating Specification: R _{abs} <0.15% @ 1900 - 2200nm
Substrate: Fused Silica IR Grade
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/8
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.60 ±0.10
Edge Thickness ET (mm): 1.43
Radius R₁ (mm): 459.00
Clear Aperture CA (mm): 22.86
f#: 39.38
Numerical Aperture NA: 0.013
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 1900 - 2200
Angle of Incidence (°): 0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View