

25.4mm Diameter x 25.4mm FL, MgF₂ Coated, PCX Condenser Lens



Stock **#15-535** [CONTACT US](#)

[Other Coating Options](#)

⊖ 1 ⊕ **€57,00**

ADD TO CART

Qty 1-10
€57,00
Qty 11+
€50,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.40 +0.2/-0.4

Effective Focal Length EFL (mm):
25.40

Numerical Aperture NA:
0.50

Substrate: Float Glass
Focal Length Tolerance (%): ±7
Coating: MgF₂ (400-700nm)
Coating Specification: R_{avg} ≤ 1.75% @ 400 - 700nm
Centering (arcmin): ≤25
Surface Quality: 80-50 (typical)
Center Thickness CT (mm): 7.20 ±0.25
f/#: 1.00
Bevel: Protective bevel as needed
Radius R₂ (mm): Plano
Shape of Back Surface: Plano
Type: Condenser Lens
Wavelength Range (nm): 400 - 700
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant