

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



High Precision Laser Grade Aspheric Lenses

Stock #39-556 3-4 DAYS

Other Coating Options



1



€730,00

ADD TO CART

Qty 1+

€730,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.05

Effective Focal Length EFL (mm):
50.80 @ 355nm

Numerical Aperture NA:
0.25

Back Focal Length BFL (mm): 45.39
Substrate: ☐ Fused Silica (Coming 7980)
Aspheric Design Wavelength (nm): 355
Asphere Figure Error, RMS @ 632.8nm: λ/40
Coating: Laser V-Coat (355nm)
Coating Specification: R _{abs} <0.25% @ 355nm
Centering (arcmin): <1
Surface Quality: 10-5
Clear Aperture CA (mm): 21.40
Edge Thickness ET (mm): 4.54
Center Thickness CT (mm): 7.98
f/#: 2
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Spot Size (μm): See Technical Information Tab
Conjugate Distance: Infinite
Note: Strehl Ratio is >0.8 by design
Damage Threshold, By Design: ☐ 7.5 J/cm ² @ 355nm, 20ns, 20Hz
Power (diopters): 19.69

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View