

TECHSPEC®

25.4mm H x 25.4mm L x 150mm FL VIS 0°, Illumination Grade PCX Cylinder Lens



Stock #36-214 3-4 DAYS

-

1

+

€88,00

ADD TO CART

Qty 1-5
€88,00
Qty 6+
€70,50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
150.00

Substrate: ☐
[N-BK7](#)

f#:
5.90551181102362

Numerical Aperture NA: 0.08
Coating: VIS 0° (425-675nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): 148.02
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 1.95
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 77.52
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant