


25.4mm Sq 30R/70T, VIS-NIR Polka-Dot Beamsplitters



VIS-NIR Polka-Dot Beamsplitters

Stock **#15-984** 3-4 DAYS

⊖ 1 ⊕ **€136,00**

ADD TO CART

Qty 1-10

€136,00

Qty 11+

€115,60

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):
0 - 45

Center to Center Spacing (mm):
0.15

Clear Aperture (%):

90
Coating: Square Aluminum (AlMgF ₂) Apertures
Construction: Polka-Dot
Dimensions (mm): 25.4 x 25.4 +0.0/-0.5
Minimum Aperture (mm): 2.00
Operating Temperature (°C): 150 Maximum
Parallelism (arcmin): <3
Reflection/Transmission Ratio (R/T): 30/70
Reflection/Transmission Tolerance (%): ±5 @ 45°
Substrate: □ B270
Surface Quality: 80-50
Thickness (mm): 1.65 ±0.1
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 2000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View