


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25.4mm Diameter Uncoated, Calcium Fluoride Window



TECHSPEC Calcium Fluoride (CaF2) Windows

Stock #11-874 3-4 DAYS



1



€145,00

ADD TO CART

Qty 1-10

€145,00

Qty 11+

€130,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
94.99

Axis Orientation:
Random

Bevel:

Protective as needed
Clear Aperture (%) : 90
Clear Aperture CA (mm) : 22.86
Diameter (mm) : 25.40 +0.0/-0.1
Thickness (mm) : 3.00 ±0.1
Coating : Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C) : 18.85
Density (g/cm³) : 3.18
Edges : Fine Ground
Index of Refraction n_d : 1.434
Knoop Hardness (kg/mm²) : 158.3
Parallelism (arcmin) : <1
Poisson's Ratio : 0.26
Substrate : Calcium Fluoride (CaF ₂) Vacuum UV Grade
Surface Flatness (P-V) : λ/2
Surface Quality : 40-20
Type : Protective Window
Wavelength Range (nm) : 200 - 7000
Young's Modulus (GPa) : 75.8

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View