

25.4mm Dia, 340 - 560nm, $\lambda/4$ Achromatic Waveplate



Achromatic Waveplates (Retarders)

Stock **#39-026** 3-4 DAYS



1



€980,00

ADD TO CART

Qty 1-5

€980,00

Qty 6+

€855,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
>20.0

Coating:
R_{avg} <0.75% @ 340 - 560nm

Diameter (mm):
25.40

Substrate: Crystal Quartz and MgF₂
Retardance: λ/4
Surface Quality: 40-20
Thickness (mm): 6.00 ±0.2
Type: Achromatic Waveplate
Dimensional Tolerance (mm): +0/-0.25
Construction: Crystalline
Transmitted Wavefront, P-V: <λ/4 @ 632nm
Parallelism (arcsec): <10
Housing Tolerance (mm): +0/-0.25
Retardance Tolerance: λ/100 @ 20°C
Coating Specification: R_{avg} <0.75% @ 340 - 560nm
Wavelength Range (nm): 340 - 560
Damage Threshold, By Design: >5 J/cm² @ 1064nm, 10ns, 10Hz
Configuration: Air Spaced

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant