

TECHSPEC®

25.4mm Protected Silver $\lambda/10$ Knife-Edge Pickoff Mirror



25.4mm Enhanced Protected Silver $\lambda/10$ D-Shaped Pickoff Mirror, #36-137

Stock **#36-137** 3-4 DAYS

-

1

+

€89,50

ADD TO CART

Qty 1-5

€89,50

Qty 6+

€80,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40

Surface Flatness (P-V):
 $\lambda/10$

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Back Surface: Fine Grind
Surface Quality: 20-10
Dimensional Tolerance (mm): +0.0/-0.20
Coating Specification: R _{avg} >98% @450 - 2000nm R _{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Edges: Ground
Parallelism (arcmin): 2
Thickness (mm): 6.35
Thickness Tolerance (mm): ±0.20
Type: Flat Mirror
Wavelength Range (nm): 450 - 10000
Damage Threshold, Reference: ☐ 0.5 J/cm ² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant