

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #15-182 3-4 DAYS



1



€1.223,00

ADD TO CART

Qty 1-4

€1.223,00

Qty 5+

€1.101,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
1064

Focal Length FL (mm):
254.00

Maximum Diameter (mm):
122

Scan Angle (°):

±25.00
Scan Field (mm): 157.0 x 157.0
Mounting Threads: M85 x 1.0
Telecentricity (°): Not Specified
Transmission (%): ≥95
Type: F-Theta Lens
Working Distance (mm): 304.6
Wavelength Range (nm): 1064
Range Distance (mm): 360.6
Focus Size Diameter, 1/e² (μm): 25
Input Beam Diameter, 1/e² (mm): 20
Maximum Length (mm): 76.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View