

TECHSPEC®

25.4mm H x 25.4mm L x 250mm FL VIS 0°, Illumination Grade PCX Cylinder Lens



Stock #36-216 3-4 DAYS

-

1

+

€88,00

ADD TO CART

Qty 1-5
€88,00
Qty 6+
€70,50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
250.00

Substrate: ☐
[N-BK7](#)

f/#:
9.84251968503937

Numerical Aperture NA: 0.05
Coating: VIS 0° (425-675nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): 248.02
Center Thickness CT (mm): 1.94
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 1.31
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 129.20
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant