

TECHSPEC®

25.4mm Silver and NIR II Coated, Corner Cube Prism



N-BK7 Corner Cube Retroreflectors with Black Overpaint

Stock #12-490 3-4 DAYS



1



€300,00

ADD TO CART

Qty 1-5

€300,00

Qty 6+

€240,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcsec):

3

Coating:

S1 Silver with protective overcoat (black overpaint) &
S2 NIR II

Diameter (mm):

25.40 +0.0/-0.1
Substrate: N-BK7
Height (mm): 19.05
Surface Quality: 60-40
Type: Retroreflector
Bevel: Protective bevel as needed
Clear Aperture (%) : 95
Height Tolerance (mm): ±0.25
Image Orientation: Left-Handed
Note: Black Overpaint is 30-60µm Thick
Coating Specification: Reflective Surfaces: R _{abs} > 97% FROM400 - 2500nm @ 0° AOI R _{avg} > 98% FROM400 - 2500nm @ 0° AOI Entrance: R _{abs} ≤1.5% @ 750 - 800nm, R _{abs} ≤1.0% @ 800 - 1550nm, R _{avg} ≤0.7% @ 750 - 1550nm
Ray Deviation (°): 180
Wavelength Range (nm): 750 - 1550
Surface Flatness (P-V): λ/8
Damage Threshold, By Design: Entrance: 8 J/cm² @ 1064nm, 10ns Reflective Surfaces: 0.5 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View