

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 25.4mm Square X -75 FL, 266nm AR Coated, Laser Grade PCV Cylinder Lens



Stock #37-580 3-4 DAYS



1



€252,00

ADD TO CART

Qty 1-5

€252,00

Qty 6+

€202,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
-75.00

Substrate: [Fused Silica](#) (Corning 7980)

f/#:
3

Numerical Aperture NA: 0.17
Coating: Laser V-Coat (266nm)
Type: Cylinder Lens, Plano-Concave
Back Focal Length BFL (mm): -77.06
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 22.86 x 22.86
Coating Specification: R _{abs} <0.25% @ 266nm
Design Wavelength DWL (nm): 266
Dimensional Tolerance (mm): +0.0/-0.025
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 5.31
Focal Length Specification Wavelength (nm): 587.6
Radius R₁ (mm): 34.39
Surface Quality: 20-10
Damage Threshold, By Design: ☐ 3 J/cm² @ 266nm, 20ns, 20Hz
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <3
Power Axis Wedge (arcmin): <3
Axial Twist (arcmin): <3

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View