

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25.4mm Square X 100 FL, 1064nm AR Coated, Laser Grade PCX Cylinder Lens



Stock #37-610 3-4 DAYS



1



€252,00

ADD TO CART

Qty 1-5

€252,00

Qty 6+

€202,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
100.00

Substrate: [Fused Silica](#) (Corning 7980)

f/#:
4

Numerical Aperture NA: 0.08
Coating: Laser V-Coat (1064nm)
Type: Cylinder Lens, Plano-Convex
Back Focal Length BFL (mm): 97.39
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.80
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 22.86 x 22.86
Coating Specification: R _{abs} <0.25% @ 1064nm
Design Wavelength DWL (nm): 1064
Dimensional Tolerance (mm): +0.0/-0.025
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 2.01
Focal Length Specification Wavelength (nm): 587.6
Radius R₁ (mm): 45.85
Surface Quality: 20-10
Damage Threshold, By Design: ☐ 15 J/cm² @ 1064nm, 20ns, 20Hz
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <3
Power Axis Wedge (arcmin): <5
Axial Twist (arcmin): <3

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View