

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #17-022 [CONTACT US](#)



1



€7.715,00

ADD TO CART

Qty 1+

€7.715,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Focal Length FL (mm):
255.00

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Model Number:
601804

Maximum Diameter (mm):
119.8 +0/-0.2

Scan Angle (°):

±18
Scan Field (mm): 114 x 114
Mounting Threads: M85 x 1
Telecentricity (°): F-Theta Only: 7.20 With Scanner: 7.40
Type: JENar Silverline F-Theta
Weight (g): 1200
Working Distance (mm): 301.50 @ 900nm 304.20 @ 1100nm
Wavelength Range (nm): 900 - 1100
Protective Window: #17-694 : One Included
Manufacturer: Jenoptik
Scan Field Diameter (mm): 160
XY Mirror Angle (°): ±6.4
Flange Distance (mm): 386.10 @ 900nm 388.80 @ 1100nm
Focus Size Diameter, 1/e² (µm): 21.0 @ 900nm 26.0 @ 1100nm
GDD Specification (fs²): 904
Input Beam Diameter, 1/e² (mm): 20
Maximum Length (mm): 97.3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View