

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 25.4mm Dia. X 88.9mm FL, NIR II Coated, Plano-Convex Lens



Stock #67-565 3-4 DAYS

[Other Coating Options](#)



1



€41,50

ADD TO CART

Qty 1-9

€41,50

Qty 10+

€37,25

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.0/-0.025

Effective Focal Length EFL (mm):

88.90 @ 587.6nm
Back Focal Length BFL (mm): 86.26
Coating: NIR II (750-1550nm)
Coating Specification: R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 4.00 ±0.10
Edge Thickness ET (mm): 2.21
Radius R₁ (mm): 45.94
Clear Aperture CA (mm): 24.4
f/#: 3.5
Numerical Aperture NA: 0.14
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 750 - 1550
Damage Threshold, Reference: ☐ 8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant