

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #14-643 3-4 DAYS



1



€243,00

ADD TO CART

Qty 1-5

€243,00

Qty 6+

€194,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):  
±3

Bevel:  
Protective bevel as needed

Coating:  
λ/4 MgF<sub>2</sub> @ 900nm on Faces  
Multilayer Dielectric on Hypotenuse

|                                                      |
|------------------------------------------------------|
| <b>Construction:</b><br>Cube                         |
| <b>Dimensions (mm):</b><br>25.0 x 25.0 x 25.0 ±0.10  |
| <b>Reflection/Transmission Ratio (R/T):</b><br>50/50 |
| <b>Reflection/Transmission Tolerance (%):</b><br>±5  |
| <b>Substrate:</b> <input type="checkbox"/><br>N-BK7  |
| <b>Surface Quality:</b><br>40-20                     |
| <b>Type:</b><br>Standard Beamsplitter                |
| <b>Wavelength Range (nm):</b><br>700 - 1100          |
| <b>Power (fringes) @ 632.8nm:</b><br>1.25            |
| <b>Irregularity (fringes) @ 632.8nm:</b><br>0.25     |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 223:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |