


25mm Dia. High Contrast IR Polarizer



Stock #36-655 3-4 DAYS

-

1

+

€1.046,00

ADD TO CART

Qty 1-9
€1.046,00
Qty 10+
€952,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°): ±20
Clear Aperture CA (mm): 22.50
Diameter (mm): 25.00
Extinction Ratio:

100,000:1
Substrate: Soda Lime Float Glass
Operating Temperature (°C): -20 to +120
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Transmission (%): >80
Type: Linear Polarizer
Dimensional Tolerance (mm): +0.0/-0.2
Construction: Nanoparticle
Clear Aperture (%): 90
Transmitted Wavefront, P-V: < $\lambda/4$
Beam Deviation (arcmin): <1
Polarization Axis Mark (%): ±2
Wavelength Range (nm): 650 - 1700

Regulatory Compliance

RoHS 2015: Compliant
Reach 197: Compliant
Certificate of Conformance: View